

## DESCRIPTION

- Enables superior precision handling of small components
- Offers a combination of comfort, dexterity and cut resistance
- Secure grip in light oily and dry conditions
- Excellent resistance to abrasion and tears for extended durability
- Black palm coating hides dirt boosting cost in use
- Treated with Actifresh to promote freshness
- Elasticated wrist provides a secure and comfortable fit

## FEATURES

- HPPE and glass liner
- Black PU coated palm up to fingers
- Level 3 cut resistance (EN388:2003)
- Breathable back of hand
- Anatomically designed



## TECHNICAL DATA

**AVAILABLE SIZES** 7/S • 8/M • 9/L • 10/XL • 11/XXL

**PACKAGING** 10/120  
*Pairs per pack/box*

**COLOUR OF LINER/COATING** Blue/Black

### TYPICAL APPLICATIONS

-  Bottling / Canning
-  Component assembly
-  Engineering
-  Glass industries
-  Packaging

**Cat**  
CE II



### EN 388 standard

Abrasion	4
Cut	3
Tear	4
Puncture	2



### Recommendations For Use

- These gloves resist cuts but are not cut proof. Do not subject to high speed or serrated blades. Do not use near moving machines if there is a risk of entanglement.
- Storage: Gloves should be ideally stored in cool, dry conditions in original packaging and away from direct sunlight.
- Cleaning/Maintenance: Both new and used gloves should be thoroughly inspected, before being worn to ensure no damage is present. Gloves should not be left in contaminated condition if re-use is intended. Not recommended for washing or cleaning as the performance characteristics may differ to washed or cleaned gloves.