

Datasheet

Art.No. 80.010.4522.1


Relay module FLARE MOVE24V-1W-AU

"standard relay module flare MOVE 24V-1W-6A, width 6,2 mm, plugable, nominal operating voltage 24V AC/DC, 1 change-over contact 250V AC / 6A, AgSnO₂ + Au; "



Art.No.	80.010.4522.1
EAN	4015573667952
Order unit	10 pieces

Approvals



Technical data

General

Connection type	Screw connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

Technical data

Type of excitation	
Rated frequency, auxiliary-/control circuit	50 - 60
Min. rated frequency, auxiliary/control current circuit	50 Hz
Max. rated frequency, auxiliary/control current circuit	60 Hz
Nominal voltage DC	24 V
Lower nominal voltage DC	18 V
Upper nominal voltage DC	28.8 V

Dimensions

Depth	76 mm
Width	6.2 mm
Height	88 mm

Classification

ECLASS 8.1	27371601: Switching relay
ETIM 5.0	EC001437: Switching relay
ETIM 4.0	EC001437: Switching relay
ETIM 3.0	EC001437: Switching relay