

## Screw connection - WP-GR HF IP66 PG21 BK - 3240948

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable gland, Pg thread, IP66 protection, with strain relief

The figure shows the WP-GR HF IP66 M12 BK version



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 710558
Weight per Piece (excluding packing)	33.93 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	82 mm
Width (a)	37 mm
Wrench size	34.00 mm
Outside diameter	28.50 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP66

#### General

Color	black
Type	With strain relief
	Outer thread
Components	free from silicone, halogen, and cadmium

# Screw connection - WP-GR HF IP66 PG21 BK - 3240948

## Technical data

### General

Inflammability class according to UL 94	V0
Material	PA

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

#### Approvals

UL Recognized / VDE Zeichengenehmigung / LR

---

#### Ex Approvals

---


#### Approvals submitted


---

#### Approval details

## Screw connection - WP-GR HF IP66 PG21 BK - 3240948

### Approvals

UL Recognized 

VDE Zeichengenehmigung 

LR

### Accessories

#### Accessories

#### Corrugated pipe

Protective hose - WP-PA HF 28,5 BK - 3240684



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Protective hose - WP-PA HF-HB 28,5 BK - 3240842



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

### Mounting material

Protective hose fixing bracket - WP-BASE A PG21 - 3241080



Fixing bracket for protective sleeves, fixed with two screws