



ENGLISH

# Data Sheet

## RS – 1364

### Humidity Temperature Meter

RS Stock No. 725-9678

#### FEATURE:

- Dual LCD with Bargraph Display for RH% Humidity, Air Temperature.
- Dew Point Reading.
- Wet Bulb Reading.
- Max / Min with Time Stamp.
- Data Hold & Relative function.
- Auto Power Off Function.
- DATA memory and read function. (99 readings from LCD display)

#### SPECIFICATIONS

<b>Measuring Range</b>	Temperature : -20 to 60°C (-4 to 140°F) Humidity : 10%RH to 95%RH
<b>Resolution</b>	0.1°C/0.1°F/0.1%RH
<b>Accuracy</b>	Temperature : ±0.5°C, ±0.9°F Humidity : ±3%RH ( at 25°C, 30 to 95% RH ). ±5%RH ( at 25°C, 10 to 30% RH ).
<b>Data Memory capacity</b>	Manual recording : 99 data sets. (Direct reading from LCD display.)
<b>Sampling Rate</b>	2 times per second
<b>Operation Temperature &amp; Humidity</b>	0 to 60°C, below 95% RH. (no condensation)
<b>Storage Temperature &amp; Humidity</b>	-10 to 60°C, below 70% RH.
<b>Power Source</b>	6 pcs size AAA Battery
<b>Battery Life</b>	Approx. 200 hours.
<b>Size</b>	150x72x35 mm
<b>Weight</b>	Approx. 235g
<b>Accessories</b>	Instruction manual, Battery and case.

