

Datasheet

Art.No. R1.190.1210.0

Configurable control component SP-COP2-EN-A DC 24V

samosPRO-Compact module, 16 safe inputs, 4 safe outputs, 4 configurable safe I/O, USB-Interface, Ethernet, Pluggable screw-terminals



Art.No.	R1.190.1210.0
EAN	4049088257766
Order unit	1 pieces

Approvals



Technical data

Connection Data

Type of electric connection	Screw connection
Detachable clamps	Yes

Output circuit

Number of outputs	8
Output current	4 A
Short-circuit protection, outputs	Yes
Type of digital output	Transistor
Min. allowed output voltage	16.2 V
Max. allowed output voltage	30 V
Number of digital outputs, integrated	8

Control circuit

Min. rated DC voltage for controls	15.6 V
Max. rated DC voltage for controls	30 V
Input current with signal 1	2.3 mA
Permitted voltage at input	30 V

Supply circuit

Min. supply voltage	16.8 V
Max. supply voltage	30 V

Dimensions

Depth	115 mm
Width	45 mm
Height	96 mm

Classification

ETIM 5.0	EC002538: Configurable control component
ETIM 4.0	EC002538: Configurable control component



Drawings

A	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	M1	M2	M3	L	0	1	11	21	11