

STANLEY

STANLEY FATMAX® Stubby Ratchet Screwdriver

FMHT0-62688



Features:

- Fine 45 tooth ratchet offering very high torque up to 3x human strength
- Soft grip handle with bit storage for added comfort and convenience
- Stubby ratchet ideal for small confined spaces
- 3 position ratchet enables clockwise, anti-clockwise and locked ratcheting positions
- FATMAX® Ratchet Screwdriver includes 6 bits
- Magnetic bit retention prevents bit loss

Description:

The STANLEY FATMAX Stubby Ratchet Screwdriver Set is ideal for screwdriving in small confined spaces, where space is limited. The fine 45 tooth ratchet offers very high torque that can deliver up to 3 times human strength for tightening, allowing you to complete the job quickly and effortlessly. Its soft handle features bit storage, saving you time searching for bits. The three position ratchet enables clockwise, anti-clockwise and locked ratcheting positions for multiple applications.

Specifications	
Colour	Black/ Yellow
Handle Material	Bi-material
Screwdriver Bit Quantity	6
Tip Type	Flat, Phillips, Pozidriv
Tip Size	Flat: 5, 6.5 mm; Phillips: PH1, PH2; Pozidriv: PZ1, PZ2