

## Screw connection - WP-G PP HF M10 - 3240995


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from PP with metric thread, IP65 protection



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 711272
Weight per Piece (excluding packing)	3.75 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	40 mm
Width (a)	20 mm
Wrench size	16.00 mm
Outside diameter	10.00 mm

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
Degree of protection	IP65

#### General

Color	gray
Type	Straight
	Outer thread
Components	Halogen-free
Inflammability class according to UL 94	HB

# Screw connection - WP-G PP HF M10 - 3240995

## Technical data

### General

Material	PP
----------	----

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

#### Approvals

VDE Zeichengenehmigung

---

#### Ex Approvals

---


Approvals submitted

---

### Approval details

## Screw connection - WP-G PP HF M10 - 3240995

### Approvals

VDE Zeichengenehmigung 

### Accessories

#### Accessories

#### Corrugated pipe

Protective hose - WP-SPIRAL PVC C 10 - 3240849



Protective hose, spring steel wire with PVC coating, highly stranded, 1 Pcs. / Pkt. = roll à 10 m

---

Protective hose - WP-SPIRAL PU C HF 10 - 3240856



Protective hose, spring steel wire with PU coating, highly stranded, 1 Pcs. / Pkt. = roll à 10 m

---