



76544 - TU 28W HALO R50/E14 240V GE TRBX 1/8

• Specifications

General characteristics:

Wattage [W]	28
Voltage [V]	240
Cap/Base	E14
Bulb Shape	R
Bulb Diameter [mm]	50
Colour temperature [K]	2800
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	2000
Dimming Capability	Yes
Coil type	2CC-8
Beam Angle [°]	35
Center Beam Candlepower [cd]	220
Maximum Overall Length [mm]	88
DUN Code	10043168765449
EAN Code	0043168765442
Net weight per piece [g]	20
Gross weight per piece [g]	33
Pack Quantity	8
Layer quantity EUR (PC)	280
Layer quantity UK (PC)	360
Pallet quantity EUR (PC)	2800
Pallet quantity UK (PC)	3600
Outer case size	202 x 103 x 95 (mm)
Brand	General Electric (GE)
Product status	Available