

## Specifications for BMP41/BMP51/BMP53 Labelmaker Tags

<b>Article No.</b>	143235
<b>Brady Material No.</b>	<a href="#">B-412</a>
<b>Material Type</b>	Polypropylene Tag
<b>Colour</b>	Black on White
<b>Finish</b>	Matt
<b>Order Reference</b>	MC-375-412
<b>Printer Compatibility</b>	BMP41; BMP51; BMP53
<b>Size - Length (m)</b>	6.10
<b>Size - Width (mm)</b>	9.53
<b>Additional Information</b>	Non-Adhesive Slide-in Strips
<b>Thickness (mm)</b>	0.201
<b>Total Qty per Pack</b>	1 Insert(s) / Box
<b>Application</b>	Broadcast Patch Bay Strips; Voice & Data Communication
<b>Industry</b>	Data & Telecommunications
<b>Layout</b>	Continuous Roll
<b>Description</b>	These tags are designed to be printed, cut to length and act as a slide-in strip for voice/data punch blocks inserts & faceplate inserts. Offers high print legibility and high tensile strength.
<b>Max. Service Temp. °C</b>	100
<b>Min. Service Temp. °C</b>	-40
<b>Shape</b>	Continuous
<b>Software</b>	LabelMark
<b>Voice/Data Application</b>	1-4 Outlet Faceplates; 110 Blocks; BIX Blocks; Broadcast Patch Bay Strips; Desi-Strip Inserts; Non-Adhesive Slide-in Strips