

Product information

18V 136MM LXT METAL SAW



Satisfying the professional's needs

BCS550Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Capacity in Mild Steel	3 mm
Depth of Cut @ 90°	51 mm
Blade Diameter	136 mm
Bore Diameter	20 mm
Noise sound pressure	101 dB(A)
Noise sound power	112 dB(A)
Noise K factor	3 dB(A)
No Load Speed	3600 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Mild Steel Tube	3 m/sec ²



STANDARD EQUIPMENT: 194204-5 18V Li-ion battery

- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- Double safety trigger.
- High comfort grips.
- LED job light that creates an easy to trace cutting line.

Details correct as of: 3-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com