



ENGLISH

Datasheet

**RS Pro Hooked Insulated Crimp Blade Terminal 16.8mm
Blade Length, 0.5mm² to 1.5mm², 22AWG to 16AWG, Red**
RS Stock No: **624-1213**



Product Details

RS Pro hooked insulated crimp blade terminal in red colour, has 16.8 mm blade length, 0.5 mm² to 1.5 mm² and 22 AWG to 16 AWG wire size. This range of funnel entry terminal guarantees total insertion of the conductor strands into the terminal barrel. The terminal design ensures a reliable electrical and mechanical connection.

Features and Benefits

- Improved contact and tensile strength due to 'rifled' barrel
- Terminal design ensures a reliable electrical and mechanical connection
- Electrolytically tin plated body with various insulation options including polycarbonate, vinyl, PVC and nylon
- Popular items also available in kits, typically stock number 613-9952

**Specifications:**

Colour	Red
Contact Material	Copper
Contact Plating	Tin
Gender	Male
Hooked	Yes
Insulation	Insulated
Insulation Material	Vinyl
Shrouded	Unshrouded
Blade Length	17.4 mm
Blade Thickness	0.75 mm
Blade Width	3 mm
Inner Diameter	4 mm
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Overall Length	27.2 mm
Wire Size	22 to 16 AWG
Current Rating	9 to 18 A
Temperature Rating	+75°C
Type	Butted Seam
Voltage Rating	600 V