

Marker pin Zack strip - BN-ZB 6,2 UV-100 - 0823504

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Marker pin Zack strip, Sheet, white, unlabeled, can be labeled with: Plotter, Mounting type: Plug in, Lettering field: 4 x 3.97 mm

The illustration shows version BN-ZB 6,2 -UNPRINTED, - CONSEC. NOS and BNB-ZB 6,2 SO/CMS



Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 332385
Weight per Piece (excluding packing)	0.24 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width (a)	6.2 mm
-----------	--------

General

Color	white
Marking mounting type	Plug in

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137

Marker pin Zack strip - BN-ZB 6,2 UV-100 - 0823504

Classifications

eCl@ss

eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 3.0	EC001694
ETIM 4.0	EC001694
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410