

General Information

Extended Product Type:	363RU6W
Product ID:	2CMA167384R1000
EAN:	7392696673846
Catalog Description:	Socket-outlet, panel mounting, 6h, 63A, IP67, unified flange, straight, 3P+E
Long Description:	Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 63A, IP67 watertight, unified flange, straight, 3-poles+earth, frequency 50-60 Hz, color code Red

Additional Information

Additional Information:	3P+E
Cable Cross-Section:	6 ... 25 mm ²
Color:	Red
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP67 / IP69
E-number:	2416746
EAN:	7392696673846
ETIM 4:	EC001317 - Panel-mounted CEE socket outlet
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001321 - CEE socket outlet
Enclosure Material:	Thermoplastic polyester (PBT)
Environmental Information:	2CMC700001D0002
Frequency (f):	60 Hz
Function:	Socket outlet, panel mounting, unified flange, straight
Gross Weight:	0.65 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#363RU6W
Minimum Order Quantity:	1 piece
Mounting Type:	unified flange, straight
Number of Poles:	4
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696673846
Package Level 1 Gross Weight:	0.65 kg
Package Level 1 Height:	139 mm
Package Level 1 Length:	112 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	112 mm
Product Main Type:	TRU
Product Name:	Industrial Socket Outlet Panel Mounting
Product Net Depth:	137 mm
Product Net Height:	137 mm

Product Net Length:	111 mm
Product Net Weight:	0.6 kg
Product Net Width:	107 mm
Protection Type:	Watertight
Rated Current (I_n):	63 A
Rated Voltage (U_r):	380 ... 415 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
Selling Unit of Measure:	piece
Short Description:	Socket-outlet, panel mounting, 6h, 63A, IP67, unified flange, straight, 3P+E
Size:	138X107X110
Standards:	IEC 60309-1 IEC 60309-2
Suitable For:	Socket Outlets for Panel Mounting
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour

