



SPECIFICATIONS

PARAMETERS	SYMBOL	VALUES			UNIT
		MIN	TYP	MAX	
Input Voltage	Vin	10	12	30	VDC
Input Current (Bright)	Iin	0.02	0.05	0.07	A
Power Consumption (MAX)	P	0.6			W
CRI	Ra	≥80 (Warm White) / ≥70 (Cool White)			
Product Life	H	50000			Hr
CCT	--	3000 (Warm White) / 6000 (Cool White)			K
Luminous Flux (MAX)	Φ	50-60 (Warm White) 40-50 (Cool White)			Lm
Operating Temperature	Topr	-20	25	40	°C

JKL PART NUMBERS: LE-3042-02-CW and LE-3042-02-WW

				METRIC DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/-		JKL COMPONENTS CORPORATION				
						TITLE 360 DEGREES LED FESTOON LAMP				
		DRAWN BY L. WENGSTROM		APPVD BY DATE L.R. 10/8/13		SIZE A	FSCM NO. 55335	DRAWING NO. LE-3042-02 MULTI		
RELEASED		10/8/13		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 10/8/13	REVISION DATE	REV. NO.	SHEET 1 OF 1
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE								