

Cable - CABLE-D37SUB/B/B/ 600/KONFEK/S - 2900760

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled, shielded round cable, with 37-pos. D-SUB socket strip on both sides; cable length 6 m



Key commercial data

| | |
|--------------------------------------|--|
| Packing unit | 1 pc |
| GTIN |  4 046356 527637 |
| Weight per Piece (excluding packing) | 1288.1 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

General

| | |
|---|--|
| Nominal voltage U_N | 125 V AC/DC |
| Max. current carrying capacity per path | 2 A |
| Max. conductor resistance | $\leq 0.09 \Omega/m$ |
| Length of cable | 6 m |
| Single wire, cross section | 0.25 mm ² |
| AWG | 24 |
| External diameter | 12 mm |
| Shielding | yes |
| | Tinned copper-braided shield, approx. 85% covering |
| Insertion/withdrawal cycles | > 200 |

Environmental conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance | IEC 60332-1 |

Connector, module side

Cable - CABLE-D37SUB/B/B/ 600/KONFEK/S - 2900760

Technical data

Connector, module side

| | |
|---------------------|--------------------|
| Number of positions | 37 |
| Connectors | D-SUB socket strip |
| Number of plugs | 1 |

Connector, controller side

| | |
|---------------------|--------------------|
| Number of positions | 37 |
| Connectors | D-SUB socket strip |
| Number of plugs | 1 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27249205 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11 | 26121620 |
| UNSPSC 12.01 | 26121620 |
| UNSPSC 13.2 | 26121620 |

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / CSA / EAC / cULus Recognized


Ex Approvals


Cable - CABLE-D37SUB/B/B/ 600/KONFEK/S - 2900760

Approvals

Approvals submitted

Approval details

UL Recognized 

cUL Recognized 

CSA 

EAC

cULus Recognized 