



Professionally approved products.

Product Datasheet

12 Metre Spring Return Hose Reel

E





RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

12 Metre Spring Return Hose Reel

A compact, professional, UPVC hose reel complete with 12mtr x 8 black air/cold water hose with a 17 bar working pressure. The hose terminates in a 3/8" bspt male fitting and is complete with 1 meter feed pipe terminating in a 3/8" bspt male. The reel is supplied complete with pivoting wall bracket.

Specification

TYPE	
Spring	Conventional Spring
HOSE	
I.D. (Inside Diameter)	8mm
Length(m)	12
Pressure(BAR)	17
No. of Hoses	1 - Single
Supplied with Hose	Yes
APPLICATIONS	
Media	Air or Water
Construction	UPVC Plastic
Max Working Temp	40°C
Weight	10 kg
SWIVEL	
Material	UPVC Plastic
Seals	Nitrile
CONNECTION	
Inlet	3/8"
Outlet	3/8"

Dimensions

