



ENGLISH

Datasheet

2491X Equipment Wire 1.5mm²

RS Stock number **361-787**



Conductor: 30/0.25mm Plain Annealed Copper
(Class 5 to IEC 60228)

Insulation: PVC (Type TI1 to BS EN 50363)

**Insulation Radial
Thickness:** 0.70mm

**Diameter Over
Insulation:** 3.40mm (Maximum)

Voltage Rating: 450/750V

**Conductor
Resistance:** 13.3 Ω /km @ 20°C (Nominal)

Cable Weight: 20.2 kg/km (Nominal)

Standard: BS EN 50525-2-31