







X-1534904-1




X-1534904-4



X-1534904-2




X-1534904-5













- Notes
- 1 MATING PART EXECUTION ACC. TO 114-18304-002
 - 2 SUITABLE CONTACTS: MQS :968220, 968221, 1534116
1,5mm CB :1241608
SEALING PLUGS 1394871 (0.63), 1394872 (1.5)
 - 3 FORM CONDITIONED DELAY OF 0,8 ADMISSIBLE
 - 4 PARTS MUST BE ORDERED SEPARATELY ACC. TO THE TABLE BELOW
- Bemerkungen
- 1 Schnittstellenausführung nach 114-18304-002
 - 2 Passende Kontakte: MQS :968220, 968221, 1534116
1,5mm CB :1241608
Dichtstifte 1394871 (0.63), 1394872 (1.5)
 - 3 Formbedingter Verzug von 0,8 zulässig
 - 4 Teile müssen entsprechend der unteren Tabelle einzeln bestellt werden

						1-1355133-1	B	LEVER / Hebel	7
						2-1355132-1	A	SHIELD, 90° REV. / Kappe, 90° gedreht	8
						0-1394909-2	B	SHIELD, 180° / Kappe, 180°	6
						1-1355132-2	A	SHIELD, 90° / Kappe, 90°	5
						0-1394911-2	A	SHIELD, 45° / Kappe, 45°	4
						1-1355135-1	A	RETAINER, 6 POSN. / Halter, 6pol.	3
						1-1355134-1	C	RETAINER, 88POSN. / Halter, 88pol.	2
						3-1355136-9	D	CARRIER HSG. / Aufnahmegeh.	1
						3-1355136-3	D	CARRIER HSG. / Aufnahmegeh.	1
QTY.	QTY.	QTY.	QTY.	QTY.	QTY.	ORDER-NO. Bestell-Nr.	REV.	DESCRIPTION Benennung	ITEM POS.
9-10-11-12 13-14-15-16	10-11-14-15	10-11-14-15	10-11-14-15	10-11-14-15	10-11-14-15	CODING Kodierung			
9-1534904-4	3-1534904-5	3-1534904-4	3-1534904-3	3-1534904-2	3-1534904-1	TYCO-REF.-NO. Tyco-Ref.-Nr.			
D	D	D	D	D	D	REV			



1-1355136-9	C	X	X	X	X	X	X	X	X
1-1355136-8	C	X		X	X	X	X	X	X
1-1355136-7	C		X	X	X	X	X		X
1-1355136-6	C		X		X	X	X	X	
1-1355136-5	C	X		X		X	X	X	X
1-1355136-4	C		X	X	X	X	X	X	X
1-1355136-3	C		X	X		X	X	X	
1-1355136-2	C	X			X	X	X		X
1-1355136-1	C	X	X	X	X	X	X		X
PART NO.	REV.	9	10	11	12	13	14	15	16
CODING									



[illegible]