



## Main

|                                    |  |
|------------------------------------|--|
| Commercial Status                  | Commercialised   |
| Accessory / separate part category | Cabling accessories  |
| Accessory / separate part type     | Pre-wired connectors                                       |
| Series name                        | General purpose  |
| Electrical connection              | Straight female connector M12, 4 pins (included earth pin) |
| Collar material                    | Metal  |
| Status LED                         | Without  |
| Cable length                       | 5 m  |

## Complementary

|                                |                          |
|--------------------------------|--------------------------|
| Cable connector fixing         | Screw-on                 |
| Cable outer diameter           | 5.7 mm                   |
| Cable composition              | 4 x 0.34 mm <sup>2</sup> |
| Wire insulation material       | PUR                      |
| [Ue] rated operational voltage | 300 V DC<br>250 V AC     |
| [In] rated current             | 4 A                      |
| Contact resistance             | <= 5000 µOhm             |
| Insulating resistance          | >= 1 GΩ                  |
| Product weight                 | 0.26 kg                  |

## Environment

|                                       |  |
|---------------------------------------|--|
| IP degree of protection               | IP67   |
| Ambient air temperature for operation | -5...80 °C (flexing)<br>-40...80 °C (static) |
| Ambient air temperature for storage   | -40...80 °C                                  |

## Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Not Green Premium product   |
| RoHS                     | Compliant - since 0649 - <a href="#">Schneider Electric declaration of conformity</a> |