




3 パネル取付推奨ネジ M3

		20	67	58	48.29	41.29	49.2	18.4	4	9	178803-8
OBSOLETE											5-178803-7
		16	59	50	40.67	33.67	41.6	18.4	4	7	178803-7
		12	51	42	33.05	26.05	34	18.4	4	5	178803-6
		10	47	38	29.24	22.24	30.2	18.4	4	4	178803-5
		6	40	31	21.62	14.62	22.6	8.4	2	2	178803-3
FINISH	POS. 寸法 DIMENSION	A	B	C	D	E	F	G	N		型番 PART NUMBER

					DIMENSION				 TE Connectivity	
					抱合電線断面(WIRE RANGE) $- \text{mm}^2 \text{ (AWG } - \text{)}$		被覆外径(INSULATION DIA.) $- \text{mm}$		名称(NAME) パネルマウント タイプ タブハウジング ダイナミック 3100 シリーズ用 WIRE TO WIRE PANEL MOUNT TYPE TAB HSG FOR DYNAMIC 3100(DOUBLE ROW)	
					材料(MATERIAL) 注記参照 SEE NOTES		仕上(FINISH)		一般公差 (GENERAL TOLERANCE) 10以下 : ± 0.2 10を超え 30以下 : ± 0.25 30を超え 100以下 : ± 0.3 角 度 : $\pm 3^\circ$	
E2	REVISED PER ECO-11-005030	RK	HMR	23MAR 11	DR. N. Matsubara 4 MAR '92	DE. N. Matsubara 4 MAR '92	SIZE A3 LOC J 番号(No.) C-178803		尺屋(SCALE) 2/1 REV. E2 SHEET 1 of 1	
LTR	変更 (REVISION RECORD)	DR	CHK	DATE	CHK. H. OBATA 4 MAR. '92	APP. S. MANABE 5 MAR. '92				