
DULUX T PLUS 18 W/840

OSRAM DULUX T PLUS | CFLni, 3 tubes, with 2-pin base for CCG operation



Areas of application

- Offices, public buildings
- Shops
- Supermarkets and department stores
- Hotels, restaurants
- Industrial lighting

Product benefits

- Very economical
- Good quality of light
- Excellent luminous flux
- Long service life
- Improved maintenance

Product features

- Average life: 10,000 h
- Color rendering index R_a : 80...89
- Short and compact pin-base lamp with triple-turn tubes
- Single-ended two-pin plug-in GX24d base



Product datasheet

Technical data


Electrical data

Nominal wattage	18.0 W
-----------------	--------

Photometrical data

Light color	840
Light color as per EN 12464-1	LUMILUX Cool White
Luminous flux at 25 °C	1200 lm
Luminance	4.7 cd/cm ²
Color rendering group	1B

Dimensions & weight



Tube diameter	12 mm
Length	124.0 mm
Length acc. to IEC standard	110 mm

Lifespan


Lifespan	10000 h ¹⁾
----------	-----------------------

¹⁾ With CCG/LLCG

Additional product data

Base (standard designation)	GX24d-2
Appropriate disposal acc. to WEEE	Yes

Light Distribution



Spectral power distribution


Equipment / Accessories

- Suitable for operation on conventional control gear
- Suitable for 0.22 A control gear only (DULUX T 18 W PLUS)

Safety advice

In case of lamp breakage: www.osram.com/brokenlamp

Product datasheet



Circuit diagram

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300333465	DULUX T PLUS 18 W/840	Shipping carton box 10	256 mm x 141 mm x 119 mm	4.30 dm ³	773.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.