

Professionally approved products.

# Datasheet

## Black Polymer Knob, M6x12

RS Stock number [448-8858](#)



### Description:

Special high-strength techno polymer in one of the Ergo style colours, matte finish. Resistant to solvents, oils, greases and other chemical agents. For push/pull applications as opposed to clamping. Thermoplastic shatterproof with brass female insert or zinc plated steel stud

### Specification:

- Body Material: Polymer
- Colour: Black
- Insert Material: Brass
- Knob Diameter: 25mm
- Knob Shape: Round
- Mounting Type: Threaded Hole
- Thread: M6 x 12
- Thread Diameter: M6
- Thread Length: 12mm

### Dimensions (mm):

L	l <sub>2</sub>	D	d	h	d <sub>1</sub>
22.5	n/a	14	25	M6	12

