

Ferrule - A 10 -12 - 3200331

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Ferrule, Length: 12 mm, Color: silver




The figure shows variant A 1-6

Why buy this product

- The A 0,25.. ferrules can also be used to process 0.14 mm² conductors
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 500 pc |
| Minimum order quantity | 500 pc |
| GTIN |  4 017918 093983 |
| Weight per Piece (excluding packing) | 0.3 g |
| Custom tariff number | 85369010 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--|--------|
| Length (b) | 12 mm |
| Inner dimension of the insulating collar (d) | 5.8 mm |
| Ferrule diameter | 4.5 mm |
| Sleeve wall thickness | 0.2 mm |

Ambient conditions

| | |
|----------------------------|--------|
| Max. permanent temperature | 105 °C |
|----------------------------|--------|

General

| | |
|----------|--------|
| Color | silver |
| Material | E-CU |

Ferrule - A 10 -12 - 3200331

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060701 |
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |
| eCl@ss 7.0 | 27400201 |
| eCl@ss 8.0 | 27400201 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |

Approvals

Approvals

Approvals

CSA / CSAus / cCSAus

Ex Approvals

Approvals submitted

Approval details

| |
|---|
|  |
|---|

| |
|-------|
| CSAus |
|-------|

Ferrule - A 10 -12 - 3200331

Approvals

| |
|--------|
| cCSAus |
|--------|
