



LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN
		P		REVISED PER ECO-11-004835	11MAR11	RK

OPENING FOR CABLE
(SEE DASH NO FOR DIA)



SIZE IDENTIFICATION
LETTER MOLDED HERE
(SEE TABLE)

#4-40 FILLISTER HEAD
STEEL SCREW
& HEX NUT
2 REQD.



.620±.015

.620±.015

CABLE CLAMP
MATERIAL: FLAME RETARDANT THERMOPLASTIC
FINISH: BRIGHT NICKEL OVER BRIGHT COPPER

#4-40 FILLISTER HEAD SCREW
STEEL
2 REQD.



- ALL PARTS PACKAGED UNASSEMBLED.
- THIS KIT CONSISTS OF 2 STRAIN RELIEF HALVES, 2 #4-40 SCREWS, 2 #4-40 NUTS & 2 #4-40 MOUNTING SCREWS.

 ZINC PLATED .000200-.000400 THICK,
CLEAR CHROMATE COATING.

B	.225	5747099-7
E	.300	5747099-5
H	.375	5747099-3
K	.430	5747099-1
SIZE IDENT LETTER	CABLE DIA	PART NO.

**COPYRIGHT 2005
TE CONNECTVITY CORP
ALL RIGHTS RESERVED**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HENNY 8-15-05	 TE Connectivity				
DIMENSIONS: INCHES		CHK C. ROHDE 8-15-05	NAME CABLE CLAMP KIT, SIZE 2, 15 POSITION, 180 DEG, AMPLIMITE SERIES, PLATED PLASTIC				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY 8-15-05					
	0 PLC ± -	PRODUCT SPEC	SIZE A2		CAGE CODE 00779	DRAWING NO C-5747099	RESTRICTED TO -
	1 PLC ± -	-					
	2 PLC ± -	-					
MATERIAL SEE CALLOUTS	3 PLC ± .005	APPLICATION SPEC	SCALE 1:1				
	4 PLC ± -	-					
	FINISH SEE CALLOUTS	ANGLES ± -	WEIGHT -	SHEET 1 of 1		REV P	
CUSTOMER DRAWING							