

Analogue Multimeters

MODEL 1110

- High sensitivity DC20k Ω /V.
- Polarity selector switch.
- 1m drop-proof heavy duty designed taut-band movement.
- Can measure line voltage up to AC 600V.
(Voltage to ground MAX AC300V)
(Protected by 600V ceramic fuse against accidental overload)
- Continuity buzzer, battery check, LED check, temperature measurement function.
- Skeleton type robust and clear case with carrying handle furnished as standard accessory.



CE

| | |
|-------------------------|--|
| DC V | 0.3V(16.7k Ω /V) \pm 3% of FS 3/12/30/120/300/600V(20k Ω /V) \pm 3% of FS |
| AC V | 12V(9k Ω /V) \pm 4% of FS 30/120/300/600V(9k Ω /V) \pm 3% of FS |
| DC A | 60 μ A/30/300mA \pm 3% of FS |
| Ω | 3/30/300k Ω \pm 3% of scale length |
| Continuity buzzer | Buzzer sounds below 100 Ω |
| LED | 10mA approx. at 0 Ω (at 3V of battery voltage) |
| Temperature | -20 $^{\circ}$ C~+150 $^{\circ}$ C \pm 3% of scale length (0 $^{\circ}$ C~+100 $^{\circ}$ C) \pm 4% of scale length (other ranges) (with the use of Temperature probe 7060) |
| Battery Test | 1.5V(0.7~2V) \pm 3% of FS (10 Ω load) |
| Maximum Circuit Voltage | 600V AC/DC (between line/neutral) 300V AC/DC (against earth) |
| Safety Standard | IEC61010-1 CAT.III 300V Pollution Degree 2 CAT.II 600V Pollution Degree 2 IEC61010-2-031 |
| Withstand Voltage | 3700V AC for 1 minute |
| Power Source | R6P(AA)(1.5V) \times 2 |
| Dimensions | 94(L) \times 140(W) \times 39(D)mm |
| Weight | 280g approx. |
| Accessories | 7066(Test Leads) 8923(F500mA/600V fuse) \times 2 R6P(AA) \times 2 9103(Carrying Case) Instruction Manual |
| Optional | 7060(Temperature Probe) |