

3M™ Fuel™ X2 Premium Series

Glasses Fuel™ X2 have a special design with a smooth profile and rimless lenses on the bottom.

Features:

- Rubber, perfectly shaped, adjustable temples
- Polycarbonate lens with the absorption of 25 to 99.9% of UV radiation
- Design with only the upper frame
- Tested according to EN166
- Soft, adjustable nose bridge
- Individually packed with bag microfiber, which, if necessary, protects and cleans the lens.
- Soft sides



Product number 7150600002

Stock Number DE272934675

Colour of lens Red mirror visor

Optical protection UV protection unbiased perception of color

Surface lens Mirror

Filter Visor 5-3.1.3M.1.FT

Use
Building
Forestry or horticulture
Light Industry & Repairs

Lens type Polycarbonate visor

Colour of frames Brown

Mechanical resistance Low energy impact and impact at extreme temperatures (-5 / +55 ° C)

Technical specifications EN 166:2001

Light transmission 17%

Features frames 3M Fuel X2 EN166 FT CE 230.1