





Invicta 63Mk2 TP&N distribution boards - 250A incoming, 63A outgoing - JK

	<i>designation</i>	<i>number of TP ways</i>	<i>glazed door cat. ref.</i>	<i>plain door cat. ref.</i>
 <p>JK206P</p>	primary boards Supplied without incoming and outgoing devices	4	JK204P	JK204P1
		6	JK206P	JK206P1
		8	JK208P	JK208P1
	One of the incoming kits listed below must be fitted.	12	JK212P	JK212P1
	See page 176 for dimensions	16	JK216P	JK216P1
		20	JK220P	JK220P1
		24	JK224P	JK224P1
 <p>JK1003S</p>	split load boards for split load configuration both switch disconnecter and RCCB incomer kits are required.	12 ways 4 RCCB protected	JK248P	JK248P1
		12 ways 6 RCCB protected	JK266P	JK266P1
		12 ways 8 RCCB protected	JK284P	JK284P1
 <p>JK0634RH</p>	switch disconnector incoming kits	100A 3P switch disconnector	JK1003S	
	* small spreader box recommended if conductors are over 35mm ²	125A 3P switch disconnector*	JK1253S	
		250A 3P switch disconnector**	JK2503S	
	** fitted in large extension box for cable spreading 500mm high	100A 4P switch disconnector	JK1004S	
		250A 4P switch disconnector**	JK2504S	
		125 3P MCCB**	JK1253M	
		160A 3P MCCB**	JK1603M	
		250A 3P MCCB**	JK2503M	
		125 4P MCCB**	JK1254M	
		160A 4P MCCB**	JK1604M	
		250A 4P MCCB**	JK2504M	
		250A 4P direct connection kit*	JK2504D	
		125A 4P + 4P manual change over switch**	JK1254CO	
		200A 3P fuse combination switch**	JK2003F	
	 <p>JK1253S</p>		200A 3P + SwN fuse combination switch**	JK2004F
		63A 4P (AC3) contactor c/w 63A switch disconnector**	JK0634C	
		100A 4P (AC3) contactor c/w 100A switch disconnector**	JK1004C	
RCCB incomer kits		63A 30mA 4P RCCB	JK0634RH	
		100A 30mA 4P RCCB	JK1004RH	
		100A 100mA 4P RCCB	JK1004RM	
		100A 300mA 4P RCCB	JK1004RL	
	100A 100mA time delayed 4P RCCB	JK1004RMD		
	100A 300mA time delayed 4P RCCB	JK1004RLD		