


MATERIALS & FINISHES:


BODY: BRASS
PLATING: SEE TABLE

CONTACT: BERYLLIUM COPPER
PLATING: GOLD 30u"

INSULATOR: TEFLON





73415-1696
4 SLOT CONTACT




ø 4.50
.177

NOTE:
73415-1696 AND 73415-1697 WITH 4 SLOTS.
ALL OTHERS WITH 2 SLOT CONTACT.

CONTACT TO BE FLUSH
- TO .004(0.10) BELOW
SURFACE



3.00
.118
4 PLACES





RECOMMENDED
MOUNTING PATTERN


73415-1699	ONE PIECE PER BAG	GOLD (1 u")
73415-1698	T&R SEE SHEET2 NOTE	GOLD (30 u")
73415-1697	73415-1696 WITH T&R SEE SHEET2 NOTE	GOLD (1 u")
73415-1696	GENERAL	GOLD (1 u")
73415-1695	73415-1690 WITH T&R SEE SHEET2 NOTE	NICKEL
73415-1694	73415-1691 PACKAGING SMALL TRAY	GOLD (1 u")
73415-1693	73415-1690 PACKAGING SMALL TRAY	NICKEL
73415-1692	73415-1691 WITH T&R SEE SHEET2 NOTE	GOLD (1 u")
73415-1691	GENERAL	GOLD (1 u")
73415-1690	GENERAL	NICKEL
PART NO.	PACKAGING	BODY PLATING

PS-89675-1830	PERFORMANCE
SPECIFICATION	DESCRIPTION

CHG: ADDED -1699	EC NO: URF2011-0644 2011/05/02 DRAWN: JWIENER CHKD: SSS 2011/05/02 APPR: JWIENER 2011/05/03	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
B2	REV			4 PLACES	± ---	± ---	DRAWN BY LMB	DATE 2000/11/9	TITLE MCX PCB/SMT JACK 50 OHM MCX-J/PCB/SMT EWR-1148	
				3 PLACES	± ---	± ---	CHECKED BY SSS	DATE 2000/11/9		
				2 PLACES	± ---	± ---	APPROVED BY JWIENER	DATE 2010/04/23	MOLEX INCORPORATED	
				1 PLACE	± ---	± ---	MATERIAL NO.	DOCUMENT NO.		
				ANGULAR ± 2 °		SEE TABLE		SD-73415-169		1 OF 2
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



SECTION B-B



SECTION D-D

NOTE:
750 CONNECTOR PER REEL ON 13 INCH REEL,
16mm TAPE, 12mm CAVITY PITCH
TAPE CAP ON EACH PART

CHG: SEE SHEET1
EC NO: URF2011-0644
DRWN: JWIENER
CHKD: SSS
APPR: JWIENER
REV: B2

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .004	± .001
3 PLACES	± .004	± .001
2 PLACES	± .004	± .001
1 PLACE	± .004	± .001

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
LMB

CHECKED BY
SSS

APPROVED BY
JWIENER

MATERIAL NO.
SEE SHEET1

DATE
2000/11/9

DATE
2000/11/9

DATE
2010/04/23

SCALE
METRIC

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

TITLE
MCX PCB/SMT JACK 50 OHM
MCX-J/PCB/SMT
EWR-1148

MOLEX INCORPORATED

DOCUMENT NO.
SD-73415-169

SHEET NO.
2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION