

# Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



16-channel VARIOFACE input relay module with screw connection and 50-pos. system connection, coil side is protected and non-isolated (optional), for Yokogawa SDV 144 cards, module width: 240 mm



## Key commercial data

Packing unit	1 pc
GTIN	 4 046356 440332
Weight per Piece (excluding packing)	684.0 g
Custom tariff number	85364900
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Width	240 mm
Height	126 mm
Depth	80 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

### Input data

Nominal input voltage $U_N$	125 V AC (120 V DC; power supply, (P1+, P2+), plug-in fuse (IEC 60127-3/IV, 1AT))
Input voltage range in reference to $U_N$	0.9 ... 1.1
Typical input current at $U_N$	4 mA ( $\pm 10\%$ per channel, pluggable fuse (IEC 60127-3/IV, 0.05AT))
Protective circuit/component	Damping diode
Type of protection	Protection against polarity reversal
Protective circuit/component	Polarity protection diode
Operating voltage display	Green LED
Status display/channel	Red LED (fuse failure display)

# Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

## Technical data

### Output data

Contact type	1 N/O contact
Contact material	Ag alloy, hard gold-plated
Maximum switching voltage	30 V AC (36 V DC)
Limiting continuous current	50 mA
Maximum inrush current	1 A (Supply 24 V DC/2 A, (P1+, P2+), pluggable fuse (IEC 60127-3/IV, 2AT))

### General

Mounting position	any
Designation	Air and creepage distances, input
Standards/regulations	EN 50178
Rated insulation voltage	150 V
Rated surge voltage	2.5 kV (basic insulation)
Pollution degree	2
Surge voltage category	II
Designation	Air and creepage distances, output
Standards/regulations	EN 50178
Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (basic insulation)
Pollution degree	2
Surge voltage category	II
Designation	Air and creepage distances, input/output
Standards/regulations	EN 50178
Rated insulation voltage	150 V
Rated surge voltage	4 kV (Reinforced insulation)
Pollution degree	3
Surge voltage category	III

### Connection data for connection 1

Connection name	Supply
Connection method	Screw connection
Number of positions	6
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section solid min.	0.34 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

### Connection data for connection 2

Connection name	Field level
Number of connections	2
Connection method	Screw connection

# Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

## Technical data

### Connection data for connection 2

Number of positions	20
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

### Supported controller

Corresponding control	YOKOGAWA ProSafe-RS
Corresponding I/O card	SDV144

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27069203
eCl@ss 7.0	27069203
eCl@ss 8.0	27371601

### ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001437
ETIM 5.0	EC001437

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Accessories

Accessories

Fuse

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Fuse - VF-SI/TR5/2AT - 2900996



Plug-in fuse (TR5<sup>®</sup>), nominal current: 2 A, tripping characteristic: slow-blow (T), packing volume per unit: 8 pcs.

---

Fuse - VF-SI/TR5/0,05AT - 2900999



Plug-in fuse (TR5<sup>®</sup>), nominal current: 0.05 A, tripping characteristic: slow-blow (T), packing volume per unit: 8 pcs.

---

Fuse - VF-SI/TR5/1AT - 2901005



Plug-in fuse (TR5<sup>®</sup>), nominal current: 1 A, tripping characteristic: slow-blow (T), packing volume per unit: 8 pcs.

---

### System cable

Cable - FLK 50-PA/EZ-DR/KS/ 100/YUC - 2900991



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 1.0 m.

---

Cable - FLK 50-PA/EZ-DR/KS/ 200/YUC - 2314299



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 2.0 m.

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/KS/ 300/YUC - 2314309



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 3.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/ 400/YUC - 2314312



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 4.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/ 500/YUC - 2321499



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 5.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/ 600/YUC - 2314927



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 6.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/ 700/YUC - 2321509



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 7.0 m

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/KS/ 800/YUC - 2314930



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 8.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/ 900/YUC - 2321512



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 9.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1000/YUC - 2314325



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 10.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1100/YUC - 2321389



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 11.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1200/YUC - 2321525



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 12.0 m

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/KS/1300/YUC - 2321392



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 13.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1400/YUC - 2321402



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 14.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1500/YUC - 2314338



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 15.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1600/YUC - 2321538



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 16.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1700/YUC - 2321541



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 17.0 m

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/KS/1800/YUC - 2321554



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 18.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/1900/YUC - 2321567



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 19.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/2000/YUC - 2314503



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 20.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/2500/YUC - 2314516



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 25.0 m

---

Cable - FLK 50-PA/EZ-DR/KS/3000/YUC - 2314529



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 30.0 m

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/KS/5000/YUC - 2318981



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 50.0 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 100/YUC - 2904739



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 1 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 200/YUC - 2904740



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 2 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 300/YUC - 2904741



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 3 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 400/YUC - 2904742



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 4 m

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/ 500/YUC - 2904636



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 5 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 600/YUC - 2904743



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 60 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 700/YUC - 2904744



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 7 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 800/YUC - 2904745



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 8 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/ 900/YUC - 2904746



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 9 m

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/1000/YUC - 2904637



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 10 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/1500/YUC - 2904638



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 15 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/2000/YUC - 2904487



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 20 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/2500/YUC - 2904639



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 25 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/3000/YUC - 2904640



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 30 m

---

## Relay Module - UM-2KS50-RM/16MR/SDV144/SO243 - 2319854

### Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/3500/YUC - 2904641



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 35 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/4000/YUC - 2904642



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 40 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/4500/YUC - 2904643



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 45 m

---

Cable - FLK 50-PA/EZ-DR/HF/KS/5000/YUC - 2904644



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 50 m

---