




LOC		DIST		REVISIONS				
P	LTR REV	DESCRIPTION MODIFICATIONS		DATE	DWN DESS.	APVD APP.		
	D1	REVISED PER ECO-11-005150		28MAR2011	RK	HMR		



COUPE A-A





Inspection hole

Ces produits ne sont pas prévus pour une utilisation automobile. Ils répondent à la norme NFC 20-130
These products are not intended for use in the car industry. They meet the standard NFC 20-130

(L)	C	B	ØA	DESCRIPTION	PART NUMBER
32	7	11	4,2	XCT 10-4	710031-1
32	7	11	5,2	XCT 10-5	710031-2
32	7	11	6,4	XCT 10-6	710031-4
39	10,5	14	8,3	XCT 10-8	710031-6
39	10,5	14	10,3	XCT 10-10	710031-8

1 - MATERIAL = TINNED COPPER
2 - Marking in depth: logo-section-hole-Made in France +
3 - CABLE SECTION = 7AWG or 10mm2
4 - GROOVE E10Cu

DIMENSIONS: mm		DWN/DESSINE D. LEGUY 15DEC00	MATERIAL MATIERE CUIVRE	TOLERANCES UNLESS OTHERWISE SPECIFIED: - TOLERANCES NON SPECIFIEES: -	
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES): 0 PLC/DEC: ±0 1 PLC/DEC: ±0 2 PLC/DEC: ±0 3 PLC/DEC: ±0 4 PLC/DEC: ±0 ANGLES ±-		CHK/VERIFIE L. MAINIER	 TE Connectivity		
		APVD/APPROUVE G. PORCHERAY			
		PRODUCT SPEC SPEC. PRODUIT	NAME TITRE	XCT 10-..	
		APPLICATION SPEC SPEC. APPLICATION	SIZE FORMAT A4	CAGE CODE 00779	DRAWING NO No PLAN C-710031
WEIGHT MASSE APPROX.		CUSTOMER DRAWING /PLAN CLIENT			

1469-35 (3/11)

20

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSIONALL RIGHTS RESERVED.
TOUS DROITS RESERVES.THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

COPYRIGHT 20