

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

LOC

DIST

G

14

REVISIONS

ZONE

LTR

DESCRIPTION

DATE

APPRO

REVISED & REDRAWN PER 0720-0283-93

9-28-93


JPD SB

WIRE RANGE

24-20 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]



NOTE:

1. WIRE INSULATION DIA 1.02 [.040] TO 2.54 [.100]

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER

1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER

1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C

VOLTAGE RATING:

-

CIRCULAR MIL AREA:
0.16 - 0.65mm² [320-1,290]
STRANDED

M7928/5-2 CLASS 2

2500

ON TAPE

2-323975-3

M7928/5-2 CLASS 1&2
MILITARY PART NUMBER & CLASS
PER MIL-T-7928

50

LOOSE PIECE

323975

QTY

PACKAGE TYPE

PART NO

DO NOT SCALE PRINT.

SPECIFIED

TOLERANCES UNLESS OTHERWISE SPECIFIED

FRACTIONS ON:

2 DEC DEC 0.201.000

3 DEC DEC 0.001.000

ANGLES 0.001.000

MATERIAL

COPPER PER ASTM B-152

NYLON, COLOR NATURAL

FINISH

TIN PLATE

PER MIL-T-10727

WEIGHT

-

OR 8-30-83

S.S. GOLDEN

CHK 8-30-83

R. HENRY

APPRO 8-30-83

S. BORTER

APPRO 8-30-83

H. BLAIR

PRODUCT SPEC

-

APPLICATION SPEC

-

-

-

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

SPlice, BUTT, P.I.D.G.,
WIRE SIZE: 24-20 AWG

SIZE

CASE CODE

DRAWING NO

B

00779

C-323975

SCALE

NTS

SHEET

1 OF 1

AMP 1478-15 REV 3-82

11 JAN 1994

15:02:04

AMPT0744

<UU128>DEPT1132>AMPT0744>U.CUSPIDG

CUSTOMER DRAWING