



**Minature  
T&B Catalog Number:**

TY125-18

**UPC Number:**

78621023103

**Status:**

Active

**Description:**

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 142mm (5.59 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

**Features**

The integrally formed nylon pawl combines low insertion and high locking strength.

**Standards**

UL Listed

**General**

Material Nylon 6.6

Color Natural

**Dimension Information**

Nominal Length (inches) 6

Length (inches) 5.34

Width (inches) 0.100

Max. Wire Bundle Diameter (inches) 1 3/8

Min. Wire Bundle Diameter (inches) 1 1/16

**Specifications**

Temperature Rating -40°F to 185°F

Flammability Rating UL 94 V-2

**Tooling**

Application Tools ERG50, QC-100, L-200, L-400-C

**Packaging**

T&B Order Multiple 1000

T&B Inner Pack 1000

Package in Units 10000

T&B Sold in UOM Each

T&B Weight Per UOM 1.25 lbs. per 1000

**Certifications**

RoHS Compliance Yes

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com