

Power Commander PDU/120V /40A/split-phase (2 x 20A)/24 pcs 5-20R O/L

4B44B2-2



Two circuits with two 20A resettable circuit breakers. Twenty-four 20A outlets with T-slots, black housing. 12' [3.6m] cord. Length 48" [1.3m].

features & benefits



specifications

Technical Information

Amps: 40
Mounting: 0U
Rated Voltage: 120V
Number Of Circuits: 2
Receptacle Type: NEMA
Network Monitoring: No
Number Of Outlets: 24

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant