

Angled brackets - BG/SHA - 1201594

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Angled brackets with M6 screw, DIN rail limit stop, for fixing DIN rails at an angle of 30°, height: 46 mm




Why buy this product

- The BG/S brackets can be used to fix DIN rails at a distance from the mounting surface
- 30° tilt angle



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 017408
Weight per Piece (excluding packing)	48.46 g
Custom tariff number	73269098
Country of origin	Germany

Technical data

Dimensions

Height	46 mm
Length	84 mm
Width	20 mm

General

Material	Steel
Coating	Galvanized, passivated with a thick layer
Color	silver

Classifications

eCl@ss

eCl@ss 4.0	23150301
------------	----------

Angled brackets - BG/SHA - 1201594

Classifications

eCl@ss

eCl@ss 4.1	23150301
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27141143
eCl@ss 7.0	27141143
eCl@ss 8.0	27141143

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC002625
ETIM 5.0	EC002625

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Angled brackets - BG/SHA - 1201594

Dimensioned drawing

