



### 3.5mm (1/8" mini) Open Frame Single Mono Jack

2-conductor phone jacks similar to Littel-Jax® phone jacks, but smaller. Perfect for connecting in limited space. Mate with 3.5 mm phone plugs with notched insulators interlock internal parts.

---

## SPECIFICATIONS

### MECHANICAL

Life: 5,000 insertion/withdrawal cycles, minimum

### ELECTRICAL

Contact Resistance: .075 ohms maximum

Insulation Resistance: 5,000 M(ohm) minimum

Dielectric Withstanding Voltage: 250V AC maximum

Contact Rating: .25A, 48V DC

### MATERIAL

Mounting Bushing: Nickel-plated copper alloy.

Insulating Spacers: Rigid plastic.

Springs: Copper alloy.

Sleeve Terminal: Tin-plated copper alloy.

Hardware: Supplied with one, Number P11501 nickel-plated brass locknut, and one, Number S17901 nickel-plated steel flat washer.