

## RS Part Number: **773-7964** Specifications and dimensions



- Boxed isolator 4 pole
- ABS plastic enclosure with padlockable handle
- Oversized enclosure to facilitate wiring

Specifications	
Height	175 mm
Width	125 mm
Depth	90 mm
Depth including switch	134 mm
Degree of protection	IP65
Rated operational current Ie AC21A	32 A
Rated operational current Ie AC22A	25 A
Rated operational voltage Ue IEC & EN	690 V
Rated operational power AC23A 380-440V	15 kW
Rated operational power AC3 440V	11 kW
Maximum gL fuse size IEC	32 A
Rated fused short circuit capacity IEC	30 kA
Knockout size	20 mm
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	6 mm <sup>2</sup>
Recommended tightening torque	1.7 Nm
Number of possible auxilliary contacts	1
Related products	
Neutral contact (early make/late break)	<b>136-5280</b>