

Datasheet

## RS Pro Straight 75Ω Panel Mount BNC Connector, jack, Crimp Termination RG179/U Nickel

RS Stock No: **738-5838**



### Product Details

RS Pro panel mount BNC connector has a nickel plated body, gold plated centre contact and is suitable for RG179/U cables. This 75 Ω straight BNC connector comes with cable jack, crimp termination.

### Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Jack, crimp termination

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Bulkhead	Yes
Cable Type	RG179/U
Contact Material	Phosphor Bronze
Contact Plating	Gold
Gender	Female
Impedance	75 $\Omega$
Mounting Type	Panel Mount
Operating Frequency	0 to 2 GHz
Polarity	Normal
Size	Miniature
Termination Method	Crimp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-40 to +50°C
Standards Met	RoHS Compliant
Voltage Rating	300 V (Working)
VSWR (Voltage Standing Wave Ratio)	1.16