

SNK series, terminal blocks

Screw clamp technology



				Terminal blocks		End sections	Jumper bars		Marking
Type	Function	Cross section IEC UL/CSA	Spacing	Rated current	Color	Order code	Order code	Nb. of poles	Order code
Fuse holder terminal blocks - For 5 x 20 mm 0.197 x 0.787 in fuses and marshalling cabinets applications									
ZS4-SF...		4 mm ² 10 AWG	6 mm 0.236 in	6.3 A 10 A	Grey, dark grey	1SNK506410R0000	Closed	2 3 4 5 10	1SNK906302R0000 1SNK906303R0000 1SNK906304R0000 1SNK906305R0000 1SNK906310R0000
		4 mm ² 12 AWG				Fuse indicator 24-110 V AC/DC 1SNK506412R0000 115-250 V AC/DC 1SNK506415R0000			
		4 mm ² 10 AWG				Fuse indicator and test 24-110 V AC/DC 1SNK506413R0000 115-250 V AC/DC 1SNK506416R0000			
ZS4-R2		4 mm ² 10 AWG	32 A 30 A	Grey	1SNK506013R0000	Closed			
ZS4-PE-R2		4 mm ² 12 AWG							
		4 mm ² 10 AWG							
		4 mm ² 12 AWG	480 A / 1s 396 A / 1s	Green-yellow	1SNK506153R0000	ES6-4S 1SNK505911R0000			MC612 MC612PA MG-CPM-13
Fuse holder terminal blocks - For 6.3 x 32 mm 0.248 x 1.259 in fuses									
ZS10-SF		10 mm ² 6 AWG	8 mm 0.315 in	10 A 22 A	Grey, dark grey	1SNK508418R0000	Closed	2 3 4 5 10	1SNK908302R0000 1SNK908303R0000 1SNK908304R0000 1SNK908305R0000 1SNK908310R0000
		6 mm ² 10 AWG							
ZS10-SF-R		10 mm ² 6 AWG							
		6 mm ² 10 AWG							
		10 mm ² 6 AWG							
Test and measurement terminal blocks									
ZS10-ST		10 mm ² 6 AWG	8 mm 0.315 in	50 A 53 A	Grey	1SNK508310R0000	ES10-ST 1SNK508910R0000	2 3 4 5 10	1SNK908902R0000 1SNK908903R0000 1SNK908904R0000 1SNK908905R0000 1SNK908910R0000
		6 mm ² 10 AWG							
		10 mm ² 6 AWG							
ZS10-ST-1		6 mm ² 10 AWG							
ZS10-ST-T4		10 mm ² 6 AWG							
		6 mm ² 10 AWG							
ZS10-R1		10 mm ² 6 AWG		57 A 62 A		1SNK508011R0000			
ZS10-PE-R1		10 mm ² 6 AWG		1200 A / 1s 1596 A / 1s	Green-yellow	1SNK508151R0000			
		6 mm ² 10 AWG							

All technical data for UL/CSA standards and dimensions in inches are shown in *italics*.

Flexible (IEC) stranded (UL/CSA) conductor - Flexible with insulated ferrule - Rigid conductor