

TradeMaster®/Spec Grade Tamper- Resistant 15A Duplex GFCI, Light Almond

1595TRLA



features & benefits

From the innovator of the product category, comes a full range of Pass & Seymour GFCI receptacles to enhance safety, shorten installation times and increase productivity on the jobsite. Our spec-grade GFCI are the most durable GFCI available. Also features patented SafeLock™ protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Light Almond

Available Colors: White, ivory, light almond, brown, black, gray, antique brass, dark bronze, nickel, titanium

Product Series: TradeMaster

Type: GFCI Receptacle

Special Features: Tamper Resistant

Style: Decorator

Listing Agencies/Third Party Information

RoHS: No

CSA Standard: C22.2 No. 42, 144

cULus: Yes

cUL Standard: Yes

Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: UL498

UL Standard: Yes

UN SPS C: 39121614

Dimensions

Depth U S: 1.13"

Height U S: 4.2"

Length U S: 4.20"

Width U S: 1.72"

Technical Information

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: WD-1, WD-6

Volts: 125V

Volts A C: 125

Grade Type: Specification

Buy American Act Compliance

Country of Origin: CHINA

Buy American Act Status: No