

## Datasheet

# 3 - 30 mm 3 Piece Cone Cutter Set

RS Stock number [221-557](#)



### Description:

A high speed, Steel tapered cone cutter for power tool use for drilling clean holes in plastic, PC boards, alloys and sheet metal up to 2 mm thick.

It has a shank length of 22 mm and a maximum shank diameter of 10 mm.

No pilot hole is required as the cutter can produce any size hole between the maximum and minimum diameters on the taper.

There is also a bright finish to the cone cutters in the set.

### Specifications:

Material: HSS

Maximum Drilling Thickness: 2 mm

Maximum Size: 30 mm

Minimum Size: 3 mm