



LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-07-007400	29/03/07	AM	FWK

NOTES

- 1 60 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 TIN PLATING
- 4 NICKEL PLATING
- 5 CHARACTERISTICS
FREQUENCY RANGE 75 OHMS: DC - 2GHz
INSULATION RESISTANCE: N/A
WORKING VOLTAGE: 250V RMS
DIELECTRIC WITHSTAND VOLTAGE: 500V RMS
TEMPERATURE RATE: -55°C TO +85°C
CONTACT RESISTANCE (CENTRE CONTACT): N/A
CONTACT RESISITANCE (OUTER CONTACT): N/A
- 6 MECHANICAL CHARACTERISTICS
DURABILITY: 500 CYCLES
- 7 FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 8 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



							1	1	TPX	INSULATOR	3
							1	1	BRASS	CONTACT	2
							1	1	BRASS	BODY	1
							5--1	5--0	MATERIAL	DESCRIPTION	ITEM
							2	1			
QUANTITY PER ASSY									PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.Morey 23/10/06		tyco Electronics Tyco Electronics Corporation Bideford, UK, EX39 4HE									
DIMENSIONS: MM		CHK S.Parlow 24/10/06											
		APVD F.Wheeler-King 24/10/06		NAME F SERIES CONNECTOR ELBOW JACK PCB 9.40 C/L									
		PRODUCT SPEC —											
		APPLICATION SPEC —											
		—											
		WEIGHT —											
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A3		CAGE CODE 00779		DRAWING NO C-1814984		RESTRICTED TO —			
CUSTOMER DRAWING								SCALE NTS		SHEET 1 OF 1		REV C	