



ENGLISH

Datasheet

RS Pro Black Coaxial Cable, Polyvinyl Chloride PVC Sheath URM202

RS Stock No: **521-8133**



Product Details

RS Pro coaxial cable in black colour, comes with PVC sheath and URM202 coaxial type. It has television aerial downleads to meet BS2316 standards. It has 7/0.25 mm plain copper stranded conductor and cellular polyethylene insulation. This coaxial cable comes in a variety of colour.

Features and Benefits

- Television aerial downleads to BS2316
- Suitable as a general purpose TV aerial downlead
- Coaxial shape

Specifications:

Attenuation	11 dB/100 m at 100 MHz, 16 dB/100 m at 200 MHz, 27 dB/100 m at 500 MHz, 40 dB/100 m at 900 MHz
Cable Shape	Coaxial
Capacitance	55 pF/m
Characteristic Impedance	75 Ω
Coaxial Type	URM202
Conductor Material	Bare Copper
Conductor Strand Type	Stranded
Connector Type	G
Core Strands	7/0.25 mm
Insulation Material	Foam PE
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-40°C
Number of Strands	7
Operating Temperature Range	-40 to +70°C
Outer Diameter	5.1
Reel Length	200 m
Sheath Colour	Black
Sheath Material	PVC
Size of Strands	0.25 mm
Velocity ratio	81%