



Datasheet

Socket Connectors

RS Stock number 458-516



Stock no.	No. of Ways	A	B	C ₁	C ₂
458-471	10	17.3	6.1	10.7	16.5
458-487	14	22.4	6.1	10.7	16.5
458-500	20	30.0	6.1	10.7	16.5
458-516	26	37.60	6.1	10.7	16.5
458-522	34	47.80	6.1	10.7	16.5
458-538	40	55.40	6.1	10.7	16.5
458-544	50	68.10	6.1	10.7	16.5



ENGLISH

Specifications:

Insulators:	Polyester GV, VO, UL 94, colour grey, RAL 7035
Operating Temperature Range:	-65°C to +150°C
Current Carrying Capacity:	1A
Tensile Strength:	1000Veff
Contacts:	Copper alloy