



mecalectro

## Small linear solenoid for intensive use – Z.8.57.AA.62 (Push)



**Stroke:** 7 mm

**Force at beginning of stroke (FM: 100/25/5%):**  
4/3/3 N

**Force at end of stroke (FM: 100/25/5%):**  
10/6/5 N

**Power Consumption (FM: 100/25/5%):**  
12/44/200 W

**Total mass:** 300 g

**Degree of protection / Energetic class:** IP 40 / B  
**Standard supplies:** 24Vcc

**Possibles supplies:** From 12 to 220Vcc

**Duty Cycle:** Permanent, impulsions (100 / 40 / 25 / 15 / 5 %)

**Standard:** NF C 79300

**Examples of applications:** Automatons, electrical equipment, machinery, security applications.