

Mini thermometer

The quick-action immersion/penetration thermometer is ideal for measuring the temperature in air, soft or powdery substances and liquids.

1 Mini thermometer, 133 mm long, up to +150°C

with protective sleeve for probe shaft

Part no.

0560 1110

2 Mini thermometer, 213 mm long, up to +250°C

with protective sleeve for probe shaft

Part no.

0560 1111

3 Water-proof mini thermometer

Protective sleeve for probe shaft

Part no.

0560 1112

Quantity discounts available

Mini penetration thermometers

- Easy to read thanks to large display
- Can be used anywhere



Technical data

	1	2	3
Meas. range	-50 to +150 °C	-50 to +250 °C	-40 to +230 °C
Accuracy	±1 °C (-10 to +99.9 °C)	±1 °C (-10 to +99.9 °C)	±1 °C (-20 to +99.9 °C)
±1 digit	±2 °C (-30 to -10.1 °C)	±2% of mv (+100 to +199.9 °C)	±2% of mv (+100 to +199.9 °C)
	±2% of mv (+100 to +150 °C)	±3% of mv (+200 to +250 °C)	±3% of mv (+200 to +230 °C)
Resolution	0.1 °C (-19.9 to +150 °C)	0.1 °C (-19.9 to +199.9 °C)	0.1 °C (-19.9 to +199.9 °C)
	1 °C (remaining range)	1 °C (remaining range)	1 °C (remaining range)
Oper. temp.	-10 to +50 °C	-10 to +50 °C	-10 to +50 °C
Battery type	Button cell LR44	Button cell LR44	Button cell LR44
Display	LCD, 1 line	LCD, 1 line	LCD, 1 line
Warranty	2 years	2 years	2 years

Accessories

Button cell batteries, Type LR 44, 1.5 Volt (4 off)

Part no.

0515 0032

Mini thermometer

Affordable. The surface thermometer has a widened measuring tip making it particularly suitable for surface measurements.

Mini surface thermometer with battery

Part no.

0560 1109

Mini surface thermometer

- Easy to read thanks to large display
- Ideal for surface measurements



Technical data

Meas. range	-50 to +300 °C
Accuracy	±1 °C (-30 to +250 °C)
±1 digit	±2 °C (remaining range)
Resolution	0.1 °C (-19.9 to +199.9 °C)
	1 °C (remaining range)
Oper. temp.	-10 to +50 °C
Battery type	Button cell LR44
Display	LCD, 1 line
Warranty	2 years

Accessories

Button cell batteries, Type LR 44, 1.5 Volt (4 off)

Part no.

0515 0032

