

KEMET Part Number: PHE840MB5100MB04R17
(F840BD103M275A)

PHE840M/F840, Film, Metallized Polypropylene, Safety, 0.01 uF, 20%, 275 VAC (X2), 760 VDC, 105°C, Lead Spacing = 15mm



Dimensions

L	18mm MAX
H	10.5mm MAX
T	5.5mm MAX
S	15mm +/-0.4mm
LL	17mm NOM
F	0.8mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	800

General Information

Supplier:	KEMET
Series:	PHE840M/F840
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
Notes:	Not For New Design, Please Check Possible Alternative Parts (AltPart)

Specifications

Capacitance:	0.01 uF
Capacitance Tolerance:	20%
Voltage AC:	275 VAC (X2)
Voltage DC:	760 VDC
Temperature Range:	-55/+105C
Rated Temperature:	105°C
Insulation Resistance:	30 GOhms
Max dV/dt:	100 V/us
Safety Class:	X2