

Datasheet

RS Pro DC Axial Fan, 120 x 120 x 25mm, 122m³/h, 3W, 24 V dc (OD1225 Series)

RS Stock No: **787-4019**



Product Details

RS Pro DC axial fan measures 120 x 120 x 25 mm. It has a power rating of 3 W and voltage rating of 24 V dc. This sealed-sleeve axial fan delivers a superior airflow of 122m³/h with a rotating speed of 1800 rpm. It is suitable for general purpose applications. The sealed sleeve technology retains bearing lubricant, increasing fan life.

Features and Benefits

- Comes in black colour
- Sealed sleeve technology retains bearing lubricant
- Long life expectancy of more than 50,000 hours

**Specifications:**

AC or DC Operation	DC
Air Flow	122 m ³ /h
Bearing Type	Sleeve
Configuration	Square
Depth	25 mm
Dimensions	120 x 120 x 25 mm
Direction of Curve	Forward
Fan Speed	1800 rpm
Height	120 mm
Maximum Current	140 mA
Noise Level	34 dB
Power Consumption	3 W
Special Features	Brushless DC, Auto Restart, Polarity Protected Motor
Static Pressure	0.1 inH ₂ O
Supply Voltage	24 V dc
Termination Type	Lead Wire
Width	120 mm
Frame Material	PBT
Impeller Material	Plastic
Insulation Resistance	10 MΩ
Life Expectancy	50000 h
Standards Met	UL, cUL, TUV

