

MB40C2

Article Number: 151-00320

Screw Fastened Bases, .18" Max tie width, .18" Hole Dia., 1.12" Length/Width, PA66, Black, 100/pkg



Download spec sheet

Base Data

Local Order Number	MB40C2
Type	MB4
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> • For use with 18 through 50 pound cable ties to provide stability when securing bundles. • Secures with two or four screws; providing multiple options. • 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.
Product Description	HellermannTyton screw fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.
Fixation Method (FF)	Screw Mounting and Rivet
Short Description	Screw Fastened Bases, .18" Max tie width, .18" Hole Dia., 1.12" Length/Width, PA66, Black, 100/pkg

Product Dimensions

Length L (imperial)	1.12 "
Length L (metric)	28.5 mm
Width W (imperial)	1.12 "
Width W (metric)	28.5 mm
Cable Tie Width Max (imperial)	0.18 "
Cable Tie Width max. (metric)	4.6 mm
Height H (imperial)	0.19 "
Height H (metric)	4.8 mm
Mounting Hole Diameter D (imperial)	0.18 "
Mounting Hole Diameter D (metric)	4.6 mm
Mounting Hole Centers (imperial)	0.8 "
Mounting Hole Centers (metric)	20.2 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	100
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

CSA Certified	No
Flammability	UL94 V2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Conformity	Yes
Certification/Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes