


ITS 31030 (RS) and ITS 41030 (RS) Rear Panel Mount Square Flange Receptacle Assembly with Lipped Backshell

ITS 31 030 RS FP 20-27 P Y XXX

- Reverse Bayonet Coupling —
- Contact Type —
31 - Solder
41 - Crimp
- 030 - Rear Wall Mount —
- Connector Backshell Class —
RS - Environmental; Supplied with
Grommet and Lipped Backshell
- Mounting Holes —
FP - Non-Threaded Through
Mounting Holes
OMIT - For Standard (Threaded)
Mounting Holes
- Mod Code Option (See Table II)
- Alternate Insert Rotation (W, X, Y, Z)
Omit for Normal (See Section A)
- Contact Gender
P - Pin
S - Socket
- Shell Size and Insert Arrangement
(See Section A)



Application Notes:

1. Rear panel mount square flange receptacle with a wire sealing grommet and backshell for use with individual wire assemblies. Threaded mounting holes. Optional non-threaded mounting holes available.
2. Connector/backshell Class "RS" (environmental)—Wire sealing grommet supplied.
3. Standard materials configuration consists of aluminum alloy. For platings, see TABLE II finish options.
4. Standard contact material consists of copper alloy with silver plating or gold plating.
5. A broad range of additional connector accessories are available.
See our website and/or contact the factory for complete information.
6. Standard insert material is synthetic rubber.
Add "FR" prefix to front of part number to specify fire resistant inserts.

ITS 31030 (RS) and ITS 41030 (RS)
Rear Panel Mount Square Flange Receptacle Assembly
with Lipped Backshell



Series ITS

TABLE I: DIMENSIONS

Shell Size	ØA +0 -0.1	K ±0.2	L Max.	M +0.2 -0	R ±0.1	S +0.2	T Thread
10 SL	18.2	2.8	43.0	18.5	18.25	25.4	M4
14 S	24.5	3.3	52.5	18.5	23.00	30.4	M4
16 S	27.2	3.3	50.5	18.5	24.60	32.5	M4
16	27.2	3.3	60.5	23.2	24.60	32.5	M4
18	30.7	4.0	60.5	23.2	27.00	35.0	M4
20	34.0	4.0	60.5	23.2	29.40	38.0	M4
22	37.3	4.0	60.5	23.2	31.75	41.0	M4
24	40.9	4.0	63.5	23.2	34.90	44.5	M4
28	46.7	4.0	63.5	24.4	39.70	50.9	M5
32	53.4	4.0	63.5	24.2	44.45	57.0	M5
36	59.6	4.0	63.5	24.2	49.20	63.5	M5
40	65.5	4.0	63.5	24.4	55.55	69.9	M5

B

TABLE II: MODIFICATION CODES

CONTACT OPTIONS	
Sym	Description
B0	Connector Less Contacts
B1	Connector with Gold Plated Contacts
Omit for standard version (Silver plated)	
FINISH OPTIONS	
Sym	Description and RoHS compliant (*)
F2	Bright Nickel Plating (*)
F6	Black Electrodeposited Paint (*)
F7	Black Zn-Co Plating (*)
F8	Olive Drab Zn-Co Plating
F11	Electroless Nickel (*)
Omit for standard version (Cadmium Olive Drab Finish)	