

## DHR263ZJ

Battery Type	Lithium-ion
Body only machine	1
Voltage	x2 18 v
Battery Capacity	Up to 4.0Ah
Max in concrete	26 mm
Max. in steel	13 mm
Max. in wood	32 mm
Impacts per Minute	0-4800 ipm
No Load Speed	0-1,200 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration: Hammer Drilling	14.5 m/sec <sup>2</sup>
Vibration: Chiselling	14 m/sec <sup>2</sup>
Vibration: Drilling into metal	3 m/sec <sup>2</sup>



- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Compact design that maintains the same easy handling and high manoeuvrability as the BHR262.
- LED Job light with pre-glow and afterglow functions
- 3 mode operation • Rotation + Hammering • Hammering only • Rotation only
- When different capacity batteries are used together, (for example 3.0Ah BL1830 and 4.0Ah BL1840, or fully charged BL1830 and 70% charged BL1830), the machine stops when the battery with less capacity gets empty.
- One touch slide chuck for SDS-plus bit.
- Ergonomic soft grip.
- Battery capacity warning lamp.
- 40 different bit-angle settings.